

Light measuring instrument 540 testo



Product in eShop

Home / [Brands](#) / [testo](#) / Light measuring instrument 540 testo

Product Data

Quick and easy-to-use instrument for measuring lighting conditions in the workplace. The sensor is adapted to spectral sensitivity of the eye.

- Display illumination
- Hold-function
- Max./min. values

Scope of supply: Meter incl. protection cap, batteries, calibration protocol

Specifications

- Measuring range: 0 to 99999 lx
- Resolution: 1 lx (0 to 19999 lx)
- 10 lx (remaining range)
- Accuracy: ± 3 lx or ± 3 %
- Measuring frequency: 0.5 s
- Dimensions (W x D x H): 133 x 46 x 25 mm
- Weight: 95 g
- IP code: IP 40
- Power supply: 2 Micro cells AAA

Item No.	type no.	Price
629.2323.93	testo 540	CHF 220.00

* The prices are non-binding and are to be understood as selling prices in Swiss francs without value added tax (VAT), as well as all other fees, charges and taxes. The prices displayed in the eShop may differ from the PDF file due to regular updates.

** Please note that when ordering chemicals and detergents, transport and packaging costs for hazardous goods as well as legally prescribed fees are charged. These will be shown in detail on the order confirmation, which you will receive in addition to the confirmation of receipt.

*** Further information such as technical information and safety data sheets can be found online in our eShop.

**** The PDF file was created on www.huberlab.ch on 04.05.2026 at 13:36 o'clock.

www.huberlab.ch