

Noise-insulating vacuum pump module for vacuum oven VO Memmert

[Product in eShop](#)

[Home](#) / [Assortment](#) / [Research & Development](#) / [Drying ovens & vacuum ovens](#) / Noise-insulating vacuum pump module for vacuum oven VO Memmert

Product Data

Item No.	description	Price
17.2018.32	Noise-insulating vacuum pump module with built-in pump (for external dimensions and material, see vacuum oven) with floor-mounted oscillating metal plate to accommodate the vacuum pump, incl. fully transparent glass door. Socket, signal cable and connecting hose to the vacuum oven VO29	CHF 6'667.00
17.2018.34	Noise-insulating vacuum pump module with built-in pump (for external dimensions and material, see vacuum oven) with floor-mounted oscillating metal plate to accommodate the vacuum pump, including fully transparent glass door. Socket, signalling cable and connecting hose to the vacuum oven VO101	CHF 7'490.00
17.2018.53	Noise-insulating vacuum pump module with built-in pump (for external dimensions and material, see vacuum oven) with floor-mounted oscillating metal plate to accommodate the vacuum pump, including fully transparent glass door. Socket, signalling cable and connecting hose to vacuum oven VO49	CHF 7'283.00

* The prices are non-binding and are to be understood as selling prices in Swiss francs without value added tax (VAT), as well as all other fees, charges and taxes. The prices displayed in the eShop may differ from the PDF file due to regular updates.

** Please note that when ordering chemicals and detergents, transport and packaging costs for hazardous goods as well as legally prescribed fees are charged. These will be shown in detail on the order confirmation, which you will receive in addition to the confirmation of receipt.

*** Further information such as technical information and safety data sheets can be found online in our eShop.

**** The PDF file was created on www.huberlab.ch on 18.05.2026 at 22:19 o'clock.

www.huberlab.ch