

Light measuring instrument SP Kern & Sohn

[Product in eShop](#)

Home / [Labortops_Q1_2026](#) / Light measuring instrument SP Kern & Sohn

Product Data

For measuring illumination of office and production workstations.

- Photo sensor: Silicon diode, filtered
- Cosine correction for angular incident light
- Data-hold function, to freeze the current measurement
- Rotating sensor unit (+ 90 and -180°) for optimum alignment to the light source
- TRACK function for continuous recording of variable environmental conditions
- Peak Hold Mode to capture peaks
- Selectable measuring units: fc (foot-candle), lx
- Battery operation

Scope of supply: Light measuring instrument, soft box with light protection, 9 V block

- Measured range: 200 ... 200,000 lx
- Material housing: Plastic
- Dimensions (WxDxH): 185 x 68 x 38 mm
- Weight: 150 g
- Battery/rechargeable battery: 1 x 9 V

Item No.	type no.	Price
17.9941.40	SP 200K	CHF 141.75

* The prices are non-binding and are to be understood as selling prices in Swiss francs without value added tax (VAT), as well as all other fees, charges and taxes. The prices displayed in the eShop may differ from the PDF file due to regular updates.

** Please note that when ordering chemicals and detergents, transport and packaging costs for hazardous goods as well as legally prescribed fees are charged. These will be shown in detail on the order confirmation, which you will receive in addition to the confirmation of receipt.

*** Further information such as technical information and safety data sheets can be found online in our eShop.

**** The PDF file was created on www.huberlab.ch on 16.05.2026 at 10:48 o'clock.