

## VACUUBRAND - Vakuum-Messgerät VACUU-VIEW



Product in eShop

Home / [Labortops Q2 2026](#) /

### Product Data

#### VACUU VIEW

- highest precision in the range from atmosphere down to 0.1 mbar, perfect gauge for all rough vacuum applications
- compact design with integrated sensor, one piece equipment for direct connect at point of interest
- chemically resistant ceramic diaphragm sensor, highly reliable at harsh laboratory conditions even in case of very aggressive chemicals
- illuminated display, easy to read
- display with menu driven handling easy to use e.g. for unit settings

Technical Data:

Measuring range: 1100 - 0,1 mbar=hPa / 825 - 0,075 torr

Measuring principle: ceramic diaphragm sensor with capacitive readabout

Accuracy of measurement: +/- 1mbar (hPa)

Vacuum connection: KF DN 16 / hose nozzle DN 6/10 mm

Dimensions (LxWxH): 50 x 62 x 103 mm

Weight: 0,19 kg

#### VACUU VIEW extended

For the monitoring of your vacuum processes in the rough and fine vacuum range, the new vacuum gauges VACUU-VIEW extended are perfect! The heavy duty combination of ceramic diaphragm sensor and ceramic jacketed Pirani sensor ensures reliable readings in the wide range from atmosphere down to 10<sup>-3</sup> mbar.

- precision and chemical resistance in an exceptionally wide range from atmosphere down to 10<sup>-3</sup> mbar, one gauge only for both rough and fine vacuum
- compact design with integrated sensors, one piece equipment for direct connect at point of interest

- the heavy duty combination of ceramic diaphragm sensor and ceramic jacketed Pirani sensor ensures reliable readings in a wide range
- illuminated display, easy to read
- display with menu driven handling, easy to use e.g. for unit settings

Technical Data:

Measuring range: 1100 - 0,1 mbar=hPa / 825 - 0,075 torr

Measuring principle: ceramic diaphragm sensor + ceramic jacketed Pirani sensor

Accuracy of measurement: +/- 15 % of indicated value in the range from 10-0,1 mbar (hPa) / +/- 3 mbar for > 10 mbar (hPa)

Vacuum connection: KF DN 16 / hose nozzle DN 6/10 mm

Dimensions (LxWxH): 50 x 62 x 103 mm

Weight: 0,19 kg

| Item No.   | designation         | Price                   |
|------------|---------------------|-------------------------|
| 17.6829.25 | VACUU VIEW          | CHF 1'212.00            |
| 17.6829.27 | VACUU VIEW extended | CHF 870.00              |
|            |                     | <del>CHF 1'377.00</del> |

### More product images



\* The prices are non-binding and are to be understood as selling prices in Swiss francs without value added tax (VAT), as well as all other fees, charges and taxes. The prices displayed in the eShop may differ from the PDF file due to regular updates.

\*\* Please note that when ordering chemicals and detergents, transport and packaging costs for hazardous goods as well as legally prescribed fees are charged. These will be shown in detail on the order confirmation, which you will receive in addition to the confirmation of receipt.

\*\*\* Further information such as technical information and safety data sheets can be found online in our eShop.

\*\*\*\* The PDF file was created on [www.huberlab.ch](http://www.huberlab.ch) on 28.04.2026 at 09:29 o'clock.